

LAMA CIRCOLARE PER SCANALATURE

DESCRIZIONE

Circolari impegnate per eseguire
SCANALATURE da D.140 a D.300 sp da
4 a 6.5 DENTE PIANO

INFORMAZIONI TECNICHE

Circolari impegnate per eseguire
SCANALATURE da D.140 a D.300 sp da
4 a 6.5 DENTE PIANO



COD. ARTICOLO	D	SP	D.FORO	Z
LMC.B.01	140	4	30-35-40	36
LMC.B.02	140	4,50	30-35-40	36
LMC.B.03	140	5	30-35-40	36
LMC.B.04	140	5,50	30-35-40	36
LMC.B.05	140	6	30-35-40	36
LMC.B.06	140	6,50	30-35-40	36
LMC.B.07	150	4	30-35-40	36
LMC.B.08	150	4,50	30-35-40	36
LMC.B.09	150	5	30-35-40	36
LMC.B.10	150	5,50	30-35-40	36
LMC.B.11	150	6	30-35-40	36
LMC.B.12	150	6,50	30-35-40	36
LMC.B.13	160	4	30-35-40	36
LMC.B.14	160	4,50	30-35-40	36
LMC.B.15	160	5	30-35-40	36
LMC.B.16	160	5,50	30-35-40	36
LMC.B.17	160	6	30-35-40	36
LMC.B.18	160	6,50	30-35-40	36
LMC.B.19	180	4	30-35-40	40
LMC.B.20	180	4,50	30-35-40	40
LMC.B.21	180	5	30-35-40	40
LMC.B.22	180	5,50	30-35-40	40
LMC.B.23	180	6	30-35-40	40
LMC.B.24	180	6,50	30-35-40	40
LMC.B.25	200	4	30-35-40	32
LMC.B.26	200	4	30-35-40	40
LMC.B.27	200	4	30-35-40	48
LMC.B.28	200	4	30-35-40	64
LMC.B.29	200	4,50	30-35-40	32

COD. ARTICOLO	D	SP	D.FORO	Z
LMC.B.30	200	4,50	30-35-40	40
LMC.B.31	200	4,50	30-35-40	48
LMC.B.32	200	4,50	30-35-40	64
LMC.B.33	200	5	30-35-40	32
LMC.B.34	200	5	30-35-40	40
LMC.B.35	200	5	30-35-40	48
LMC.B.36	200	5,50	30-35-40	32
LMC.B.37	200	5,50	30-35-40	48
LMC.B.38	200	6	30-35-40	32
LMC.B.39	200	6	30-35-40	48
LMC.B.40	200	6,50	30-35-40	32
LMC.B.41	200	6,50	30-35-40	48
LMC.B.42	250	4	30-35-40	40
LMC.B.43	250	4	30-35-40	60
LMC.B.44	250	4	30-35-40	80
LMC.B.45	250	4,50	30-35-40	40
LMC.B.46	250	4,50	30-35-40	60
LMC.B.47	250	5	30-35-40	40
LMC.B.48	250	5	30-35-40	60
LMC.B.49	250	5,50	30-35-40	40
LMC.B.50	250	5,50	30-35-40	60
LMC.B.51	250	6	30-35-40	40
LMC.B.52	250	6	30-35-40	60
LMC.B.53	250	6,50	30-35-40	40
LMC.B.54	250	6,50	30-35-40	60
LMC.B.55	300	4	30-35-40	48
LMC.B.56	300	4,50	30-35-40	48
LMC.B.57	300	4	30-35-40	72
LMC.B.58	300	4,50	30-35-40	72
LMC.B.59	300	5	30-35-40	48
LMC.B.60	300	5	30-35-40	72
LMC.B.61	300	5,50	30-35-40	48
LMC.B.62	300	5,50	30-35-40	72
LMC.B.63	300	6	30-35-40	48
LMC.B.64	300	6	30-35-40	72
LMC.B.65	300	6,50	30-35-40	48
LMC.B.66	300	6,50	30-35-40	72